



Technical Data

Color	Black
Sizes Available	9.75-10.5
Packaging	Bagged Pair
Packed	32 Pair/Case
Case Dimensions (in)	33.50 x 25.50 x 26.50
Case Weight (lbs)	64.00
Country of Origin	United States
Polymer	Butyl
Grip	Smooth
Cuff	Rolled
Length	32"
Powder	Powder Free
Thickness	15 Mil
Construction	Waterproof, Supported
Certifications	TAA Compliant

North®

15 Mil, 8" Port Ambidextrous Butyl Glovebox Glove - 32"

- Butyl is a soft and flexible material and it provides the highest permeation resistance to vapors and gases while also reducing hand fatigue to enhance worker comfort
- Highly resistant to ketones (MEK, MIBK, acetone) and esters (tricresyl phosphate, amyl acetate, ethyl acetate)
- Particularly suited to applications involving highly toxic chemical hazards such as chemical weapons
- Rolled bead cuff resists tearing, improves donning strength and maintains a secure seal on glovebox ports
- Smooth finish for low friction, improved dexterity, and precise glovebox handling
- Options available in 9.75" and 10.5" hand sizes (palm diameters)
- Ambidextrous construction allows for use with either hand
- Made in the USA

Care Instructions

Four year shelf life when stored in original packaging in a cool dry place away from light. Recommended temperature range: 50F to 86F (10C to 30C)

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
8B1532A/9Q	Black	9.75	883940165677		00883940165431
8B1532A/10H	Black	10.5	883940165660		00883940165424