Sawyer | E42052-OK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A wood-framed mirror is offered in a choice of Walnut or Distressed Oak, combining natural elements with modern functionality. A 2-inch frosted band along the frame's interior is backlit with LEDs, providing optimal illumination above a vanity. A discreetly hidden control along the edge of the frame allows easy selection between 3000K, 4000K, and 5000K color temperatures for personalized lighting.



MEASUREMENTS

DIMENSION	: 24" W x 32" H x 2" Ext
HANGING WEIGHT	: 32.34 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 5,200 Rated (1,800 Del.)
BULB	: 1 x 52W LED DC Integrated , 52W Total
BULB INCLUDED	: (Integrated)
CRI	: 90 CRI
COLOR_TEMP	: 30-40-50K

FINISHES OPTION

Oak (OK)
Walnut (WN)

MATERIAL

Wood, Steel, Glass

RATINGS

cETLus
Damp Location
CA Title 24
ADA

ADDITIONAL

RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com