Reeds | E11010-144BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A refined play of texture and proportion, this series juxtaposes vertically fluted aluminum housings with linear reeded glass tubes. Offered in Gold or Matte Black finishes, each form integrates frosted glass diffusers that soften the powerful LED illumination within. Designed for architectural flexibility, the collection includes ADA-compliant sconces, a minimalist stem-hung GU10 pendant, adjustable GU10 spotlights, and an additional flush mount. Universal dimming and commercial-grade drivers make it ideal for elevated residential, hospitality, or decorative commercial settings.



*Height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION	: 5" W x 16" H x 3.75" Ext
MAX OAH	: 5" W x 5" H
HANGING WEIGHT	: 2.2 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 400 Rated (240 Del.)
BULB	: 1 x 5W LED PCB Integrated , 5W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Black (BK)
Gold (GLD)

GLASS

Clear Ribbed 144

MATERIAL

Steel, Aluminum, Glass

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: UP/DOWN
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com