



5592TRM  
Tub/Shower Trim  
**Specification Submittal**

Location:

**Model Numbers**

- 5592TRM**  
Tub/Shower Trim

**Valve Options:**

- 262 Series Temptrol® Shower Valve with TRM modifiers
- 162 Series Temptrol Shower Valve requires TC modifier

**Feature Highlights**

- Elm Tub/Shower Trim.
- Requires Temptrol® Pressure-Balancing Shower Valve.
- Metal lever handle.
- 5-1/4" Slip-on diverter tub spout.
- 7-mode HydroMersion showerhead with Non-Positive Shutoff (NPSO).
- Standard 2.0 gpm (7.6 L/min) flow restrictor.
- Components shall be metal and nonmetal construction, plated in standard Polished Chrome finish.

**Compliance**

- ASME® A112.18.1/CSA® B125.1
- WaterSense® 1.5 gpm (5.7 L/min) 2.0 gpm (7.6 L/min)
- Lever handle meets ADA requirements for operation



**Options/Modifications**

- 15 GG** 1.5 gpm (5.7 L/min) flow restrictor
- L1** Less showerhead
- L4** Less head, arm, and flange
- L7** Less handle
- TC** Test Cap Trim (includes TA-10™ & T-12A) *used with 162 Series Temptrol Shower Valve*
- BBZ** Brushed Bronze finish
- MB** Matte Black finish
- STN** Satin Nickel finish

**Warranty**

**Limited Lifetime** - for residential installations.

**10 Years** - for commercial/industrial installations.

Refer to [www.symmons.com/warranty](http://www.symmons.com/warranty) for complete warranty information.



**SKU Builder**

Series	Finish	Modifier	Flow Rate	TRM (required)	TC	Final SKU
5592	STN		15	TRM		5592STN15TRM
5592	MB	L1		TRM	TC	5592MBL1TRMTC

**Notes:** No more than two modifiers (L1-L7) permitted when ordering. Modifiers will list in numerical order.

**Architectural/Engineering Specification**

Symmons Elm Tub and Shower Trim \_\_\_\_\_ Includes Elm Tub/Shower Trim for Temptrol Pressure-Balancing Shower Valve. Features metal lever handle, 5-1/4" Slip-on diverter tub spout, 7-mode HydroMersion showerhead with NPSO, and standard 2.0 gpm (7.6 L/min) flow rate. Components shall be metal and nonmetal construction, plated in standard Polished Chrome finish. 10-Year Commercial Warranty. ASME A112.18.1/CSA B125.1, WaterSense 1.5 gpm (5.7 L/min) and 2.0 gpm (7.6 L/min) compliant. Lever handle meets ADA requirements for operation. Available options: 15 = 1.5 gpm (5.7 L/min) flow restrictor, L1 = Less showerhead, L4 = Less head, arm, and flange, L7 = Less handle, TC = Test Cap Trim, BBZ = Brushed Bronze finish, MB = Matte Black finish, and STN = Satin Nickel finish.

