

# MAGNETIC STIRRER

PCE-MSR 100L



## Specification

Speed	
Measuring range up to	100 ... 600 U/min
Resolution	5 U/min
Accuracy	10 U/min

General technical data	
cable length	1,5 m
Display Typ	LCD
Dimensions	Platform: 400x400 mm Control panel: 210x75 mm Stirring paddle: 160 mm
Performance	120 W
Number of stirring points	1
Drive of the stirring points	Brushless motor
Max. Stirring quantity	100 L
Stirring plate material	Stainless steel smooth sheet
Timer from	1 min.
Timer until	24 h
Max. Stirring viscosity	34 cp
Protection class (device)	IP21
Power supply	100 ... 240 VAC
Connector type	Earthing contact plug
Operating conditions	5 ... 40 °C , 80 %RH
Storage conditions	0 ... 50 °C , 80 %RH
Dimensions ( L x W x H )	400 x 400 x 95 mm
Weight	7800 g