

YS26A1, Al Compression Splice, 2/0 AWG, AL9CU

By Burndy
Catalog # [YS26A1](#)

2/0 AWG, AL, SPLICE, AL9CU



Features

- Aluminum splices are dual rated to accommodate both copper and aluminum wire
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX™ Type A13 oxide inhibitor
- Color coded end caps inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel

Application

Wire Splice

Specifications

| | |
|------------------------------------|---|
| Certification - UL Recognized | No |
| Buy American Compliant | No |
| Certification - cULus | No |
| EU RoHS Indicator | Yes |
| Buy America(n) Qualified | TAA Compliant (All status valid till December 2026) |
| Industry Standard(s) | UL 486A-486B |
| Certification - ETL | No |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |
| Certification - CSA Approved | Yes |

Conductor

| | |
|-------------------------------------|--|
| Conductor - Material | ALUMINUM / COPPER |
| Wire Size | <ul style="list-style-type: none"> • 700 KCMIL • 750 KCMIL |
| Conductor - AL Str Size | 2/0 AWG |
| Conductor - AL Str Size Range | 2/0 AWG |
| Conductor - Copper Str Size | <ul style="list-style-type: none"> • 700 KCMIL • 750 KCMIL |
| Conductor - Copper Str Compact Size | 2/0 |
| Conductor Size | 2/0 AWG |
| Conductor Type | CODE |

Conductor - Copper Str Size Range 2/0 AWG

Configuration

Connector Type DUAL RATED

Current

Voltage Rating 35 kV
Voltage - Maximum 35000

Dimensions

Package Height 0.000 in
Package Weight 0.000 lb.
Package Length 0.000 in
Outside Diameter 0.67 in
Package Width 0.000 in
Dimension - L Length Overall mm 66 mm
Dimension - Outside Diameter inch 0.67 in
Dimension - Strip Length inch Length 1-3/8 in 2.61 in
Dimension - B Length fraction 1-3/16 in
Dimension - B Length inch 1.18 in
Dimension - Length Overall inch 2.61 in

General

Trade Name HYLINK™
Die Index 297
Feature - Barrel Type Long
Feature - Barrel Style Chamfered
Plated Y
Color Code Olive
Sub Brand HYLINK
UPC 781810757109
Type YS-A, Standard Barrel
Material Aluminum
Plating Type Tin - Electro Plated
Finish Type Tin-Plated
UPC 12 Digit 781810757109
UPC 14 Digit GTIN 00781810757109

Logistics

Minimum Pack Quantity 1

Carton Quantity 5

Product Assets

Operational

[Catalog \[English\]](#)

Temperature Rating 194



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YS26A1-SPEC-EN | REV 5/2026