

CAMBRIDGE

MDS121-AGB/CRN

The Cambridge family features refined, metal drum shades with sleek details. The brass interior of the chandeliers amplifies light when illuminated, creating a warm, atmospheric glow. Strips of metal with visible screws add a modern touch, giving each fixture a distinctive industrial flair. Available in 4 and 6-light formats, Cambridge is well-suited to a dining room or kitchen. Available in three finish options, Aged Brass and Soft Studio Green, Aged Brass and Soft Crimson and Polished Nickel and Soft French Blue.

FINISHES

AGED BRASS w/ SOFT CRIMSON

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 23"

Width/Diameter: 28.5"

Minimum Height: 28"

Maximum Height: 77"

Canopy/Backplate: 4.75"

Hanging Type: 54" Chain

Product Weight: 25.3lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

Shade

Shade 1: Metal

Shade 1 Top Width: 22.25"

Shade 1 Bottom L/W: 0" / 28.5"

Shade 1 Height: 12.25"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 60

Bulb Quantity: 6

Bulb Included: No

Wire Length: 120"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 33" x 33" x 22"

Carton 1 Weight: 29lb

Shipping Method: Truck Only

Country of Origin: VN

