

# ACTIVARMR<sup>®</sup>

PERSONAL PROTECTIVE GEAR

## 80-400

Hi-Viz<sup>™</sup> insulated glove

Previously known as: Powerflex<sup>®</sup> 80-400



Cold



Medium Duty

## Fleece-lined work gloves, ensuring safe and comfortable handling in cold conditions

- **Heightened visibility:** These high-visibility safety gloves offer cut and abrasion protection in poor light conditions, with a seamless bright yellow terry loop acrylic liner
- **Reinforced grip:** ActivArm<sup>®</sup> 80-400 thermal gloves feature a bright blue crinkled palm finish, enhancing grip in wet and dry conditions
- **Optimized insulation:** Fleece-lined, with a natural latex coating, these thermal work gloves guard against temperatures as low as  $-15^{\circ}\text{C}/5^{\circ}\text{F}$  (extended contact) and  $-30^{\circ}\text{C}/-22^{\circ}\text{F}$  (intermittent/short contact), but are also able to handle hot components up to  $250^{\circ}\text{C}/480^{\circ}\text{F}$  for 15 seconds
- **Advanced ergonomics:** ActivArm<sup>®</sup> 80-400 industrial gloves' ergonomic design grants users superior fit and comfort, while ensuring flexibility and dexterity



### Industries

- Construction
- Forestry

### Applications

- Shipping and loading of product
- Construction
- Outdoor Winter Use

# ACTIVARMR®

PERSONAL PROTECTIVE GEAR

## 80-400

Hi-Viz™ insulated glove

Previously known as: Powerflex® 80-400

### Key Features

- **High-visibility design:** For personal protection in poorly lit environments
- **Crinkled palm coating:** Enhanced wet and dry grip
- **Fleece lining:** For assured low-temperature hand protection

### Performance Standards & Regulatory Compliance

REACH Compliant



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
ActivArm <sup>®</sup> 80-400	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Natural Latex Rubber <b>Liner Material:</b> Acrylic Terry Loop <b>Cuff Style:</b> Knitwrist	7	7, 8, 9, 10, 11	250 - 290 mm, 10-12"	Blue	• 12 pairs in a bag; 6 bags in a carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.