



Project / Job Name:

Location:

Fixture Type:

Notes:

S16514 - 10 Watt T5 LED; 21 Inch; 35K/4K/5K/65K; G5 Base; Type A; Omni



GENERAL

Company	SATCO
EA Height	0.75
EA Width	0.75
EA Length	21.06
Lamp Ballast Type AB	Type A
Ballasting Requirements	Ballast required, check compatibility
Material	Polycarbonate (PC)
Fixture Type	Miniature
Status	Active
Total Harmonic Distortion	Ballast Dependent
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	White
Amps	Ballast Dependent
Lens Finish	Frost
Lens Material	Glass
Nominal Length	21.0
Operating Position	Universal
Power Factor	Ballast Dependent
SDS Class	LED_Lamp
Shatter Proof Type	PET Coated
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	13W

ELECTRICAL

CCT (Kelvin Temp)	3500K/4000K/5000K/6500K
Hours Rated	36000
Beam Angle (degree)	180
Color Temp	Neutral White to Daylight
CRI	80+
Operating Frequency	50/60Hz
Operating Temp	-4F to +113F (-20C to +45C)
Lumens	1400L
Volts	Ballast Dependent
Watts	10W

PHYSICAL

Lamp Base	Miniature Bi Pin
Finish	Frost
ANSI Base	G5
Lamp Type	T5
MOD Lamps	0.62
MOL	20.91

ADDITIONAL INFO

Warranty	3-Years
Rated For Enclosed Fixture	Yes

PACKAGING

UPC	045923165146
Case Cube	0.2724
Case Height	4.72
Case Length	23.03
Case Quantity	25
Case UPC	10045923165143
Case Weight	4.2
Case Width	4.33
EA Cube	0.0069
EA Height	0.75
EA Length	21.06
EA Quantity	1
EA Weight	0.15
EA Width	0.75
Pack Type	Sleeve
Web Length	20.91
Web Width	0.62

COMPLIANCE

Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
Title 20	Exempt
T24/JA8 Compliant	No