

SHANETTE

H1128101-VGL

Shanette elevates a simple, rounded sconce form with statement materials. The soft white swirls of the Piastra glass shade create the illusion of gentle motion when illuminated. A metal reflector in Vintage Gold Leaf adds depth and dimension behind the light, complementing the gold pins at the front of the fixture. This softly poetic piece is suitable for any space.

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 12.5"

Width/Diameter: 10.75"

Length: 4.25"

Canopy/Backplate: 4.75"

Product Weight: 4lb

Extension: 4.25"

Top to Center: 5.5"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Piastra

Shade 1 Top Width: 9.25"

Shade 1 Height: 2"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 17" x 16" x 7"

Carton 1 Weight: 7lb

Shipping Method: Ground

Country of Origin: VN

