



jalas® E-SPORT 1625

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2011 S3, SRC, CI, HI

Learn more

Safety boot, nail protection material plasma-treated composite (PTC) textile, toecap material aluminium, plastic shank, PU outsole, upper material PU-coated leather, Split leather

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Good shock absorption
- Light

FUNCTIONS

- Low weight
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Padded boot shaft
- Ventilating insole
- Water repellent
- Reflector
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, Environments with risk for outsole penetration

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Regular
COLLECTION E-Sport
UPPER MATERIAL PU-coated leather, Split leather
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester, polyamide
INSOLE JALAS FX2 Classic
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Shock absorption zone in Ergothan
OUTSOLE MATERIAL PU outsole
FASTENING Laces
SHOELACES LENGTH 120 cm
COLOUR Black
NET WEIGHT, (SIZE 42) 1.21 kg

COMPLIANCE

CE Cat. II

ASTM F2413-18
M/I/C/SD 35/PR

EAC

EN ISO 20345:2011
S3, SRC, CI, HI

TP TC 019:2011

FEATURES

- Aluminium toecap
- Nail protection in plasma-treated composite (PTC) textile
- Water repellent
- Oil-resistant outsole
- Ergothan Shock Absorption System
- Stabilizator
- Anti-static properties
- ESD

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	1625-36	6408487438639
37	4	5	6	1625-37	6408487438646
38	5	5.5	6.5	1625-38	6408487438653
39	6	6.5	7.5	1625-39	6408487438660
40	6.5	7.5	8.5	1625-40	6408487438677
41	7	8	9	1625-41	6408487438684
42	8	9	10	1625-42	6408487438691
43	9	9.5	11	1625-43	6408487438707
44	10	10.5	11.5	1625-44	6408487438714
45	10.5	11	12.5	1625-45	6408487438721
46	11	12	13	1625-46	6408487438738

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.