Project / Job Name:

Location:

Fixture Type:

Notes:



62-3243 - Huntington; 18-Inch LED Vanity; 20 Watt; 3000K-1800K CCT; Dark Bronze Finish; Faux Alabaster Glass

GENERAL

Company	NUVO
EA Height	6.25
EA Width	5.0
EA Length	19.38
Mounting Height	4.38
Mounting Length	18.0
Mounting Width	4.38
Bulb Included	Integrated
Extends (in)	4.38
Material	Steel
Includes	Screws and Plastic Anchors
Status	Active
Style	Modern and Contemporary
Surge Protection	Built-in surge protection - 1.5KV
Total Harmonic Distortion	<45%
Top To Outlet	2.13
Up Down Installation	Universal
CCT Selectable	Yes
Wattage Selectable	No
Collection	Huntington
Finish Family	Bronze
Amps	0.190A
Lens Finish	Faux Alabaster
Lens Material	Acrylic
Nominal Length	18.0
Power Factor	>0.9
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	26W
Incandescent Equivalent	105W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K-1800K
Dimmable	Yes-Dimmable
Hours Rated	30000
Beam Angle (degree)	120
Color Temp	Soft White to Warm White
CRI	95+
Dimming Type	Phase Cut (TRIAC)
Operating Frequency	60Hz
Operating Temp	-40F to +194F (-40C to +90C)
Lumens	1600L
Volts	120v
Watts	20W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Dark Bronze
Housing Color	Dark Bronze
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Rectangle

ADDITIONAL INFO

Warranty	3-Years
Rated For Enclosed Fixture	No

PACKAGING

UPC	045923416750
Case Cube	0.3505
Case Height	6.25
Case Length	19.38
Case Quantity	1
Case UPC	10045923416757
Case Weight	7.15
Case Width	5.0
EA Cube	0.3505
EA Height	6.25
EA Length	19.38
EA Quantity	1
EA Weight	7.15
EA Width	5.0
Pack Type	Kraft Box
Web Height	4.38
Web Width	18.0

COMPLIANCE

ADA Compliant	No
Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	Yes

© Satco Products, Inc.
All rights reserved 2026