



Mechanical Dimensions: Inches [mm]

Tolerances ± 0.012 [0.3] Unless Otherwise Specified



Mounting Hole



Thickness: IN[mm]max

Electrical Specifications

Rating	30A @24VDC
Contact Resistance	-20°C ~85°C

Material Specifications

	LED Indication of a Blown Fuse
Body Material	Nylon (UL Flame: 94V-2)
Cap Material	Polycarbonate (UL Flame: 94V-2)
Terminal Material	Brass, Tin-Plated
Terminal Type	0.250" (6.4mm) Quick Connect
Panel Thickness	0.5~7.0mm
Mounting	Snap-in

**Regular (ATO/ATC Style)
Blade Fuse Block**

BLR-I-301



Rev	Date of issue	Revision Notes	Designed	Approved
C	07-21-2025	Initial Drawing	RC	OF