

JOVANI

B1809-PBR/SSD

A modern interpretation of Art Deco shapes, the Jovani bath bar features elongated arms and sharply tapered Soft Sand shades. The clean design highlights the connections between elements through pronounced fittings and subtle fluting details. Finished in classic Patina Brass, Jovani is available with 1, 2, or 3 lights.

FINISHES

PATINA BRASS w/ SOFT SAND

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 10.25"

Width/Diameter: 7.75"

Canopy/Backplate: 4.75"

Product Weight: 1.8lb

Extension: 9"

Top to Center: 4.25"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Steel

Shade 1 Finish: Soft Sand

Shade 1 Bottom L/W: 0" / 7.75"

Shade 1 Height: 4"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 10" x 10" x 10"

Carton 1 Weight: 3lb

Shipping Method: Ground

Country of Origin: VN

