

YSR6CFX10CLTCKITC

Attributes	Values
Application	Wire Reducing Splice
AWG Size	10 AWG - 6 AWG
Barrel Style	Skived
Barrel Type	Standard
Coating	Tin-Plated
Collection Name	HYREDUCER
Color Code	Blue
Cond. Material	Copper
CSA Approved	No
cUL Approved	No
cULus Approved	No
Die Index	7;
ETL Approved	No
Height (in)	0.21
Length (in)	1.53
Length L2 (in)	0.73
Material	Copper
Plated	Yes
Plating Type	Tin - Electro Plated
Power Cond. AWG Size	6 - 10 AWG
Strip Length (in)	0.7
Temperature Rating	194 Deg C
Voltage	35 kV
Width (in)	0.31