Product Offering

	Cat. No.	Case Quantity	Colour	Thickness	Low Temperature rating	High Temperature rating	Adhesion Strenght	Elongation in %	Tensile Strength	Dielectric Strength
Premium Professional	46-33	10	Black	7 mil	0˚F -18˚C	221˚F 105˚C	20 oz/in.	260	17 lb/in.	9,000V
	46-88 *			8.5 mil				300	20 lb/in.	10,000V
	46-35-WHT		White	7 mil	14˚F -10˚C			200	17 lb/in.	7,500V
	46-35-BLU		Blue							
	46-35-RED		Red							
	46-35-GRN		Green							
	46-35-YLW		Yellow							
	46-35-ORN		Orange							
	46-35-BRN		Brown							
	46-35-GRY		Grey							
	46-35-VIO		Violet							
Contractor PRO	46-PRO	10	Black				17 oz/in.	220		
General Purpose	46-1700	10	Black		32˚F 0˚C	176˚F 80˚C	16 oz/in.	200	16 lb/in.	7,000V
	46-1700-WHT		White							
	46-1700-BLU		Blue							
	46-1700-RED		Red							
	46-1700-GRN		Green							
	46-1700-YLW		Yellow							
	46-1700-ORN		Orange							
	46-1700-BRN		Brown							
	46-1700-GRY		Grey							
	46-1700-VIO		Violet							

LISTED
E499283