Framed | E42092-GLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

MEASUREMENTS

DIMENSION	: 24" W x 36" H x 1.5" Ext
HANGING WEIGHT	: 39.6 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 4,200 Rated (1,050 Del.)
BULB	: 1 x 42W LED PCB Integrated , 42W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Dimmable on touch switch
CRI	: 90 CRI
COLOR_TEMP	: 3000-4000-5000K
LIGHTING_DIRECTION	: Indirect

FINISHES OPTION

- Black (BK)
- Gold (GLD)
- Satin Nickel (SN)

MATERIAL

Steel, Glass

RATINGS

cETLus
Damp Location
CA Title 24

ADDITIONAL

INSTALL UP/DOWN: Vertical / Hori
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com