



Bouton® Optical OverSite™

OTG Rimless Safety Glasses with Black / Gray Temple, Clear Lens and Anti-Fog / Anti-Scratch Coating

- Over-the-glass design helps keep prescription eyewear users in compliance
- Can also be worn by itself as a regular safety glass
- Rimless frame design ensures an unobstructed view
- Adjustable length temples are rubber co-molded, offering the user a secure custom fit
- Ratchet temples for better angle adjustment
- Molded nose bridge design to fit the vast majority of users
- U-Fit® spatula temples
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Fits Comfortably Over Personal Eyewear
- General Manufacturing
- Construction Applications
- Indoor Work

Technical Data

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	26.85 x 11.22 x 15.08
Case Weight (lbs)	16.53
Country of Origin	Malaysia
Lens	Clear
Frame Style	Over-The-Glass
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch, Anti-Fog
Bridge	Molded
Temple	Adjustable Length, Co-Molded, Tilt Adjustment
Base Curve	3
Certifications	ANSI Z87.1, EN 166, EN 170, EN 172
Product Circularity	Recycled via Terracycle

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-98-0000	Black	Clear	Clear	AS	616314131165	01616314131164	02616314131163
250-98-0013	Black	IR Filter	Green	AS	616314131172	01616314131171	02616314131170
250-98-0020	Black	Clear	Clear	AS/AF	616314161964	01616314161963	02616314161962
250-98-0024	Black	IR Filter	Green	AS/AF	616314267277	01616314267276	02616314267275
250-98-0080	Black	Clear	Clear	U	616314131158	01616314131157	02616314131156

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated