






PRODUCT DESCRIPTION

The classic cube form has become a staple in modern lighting design. These products have been designed with minimal extension for ADA compliance. The smaller downlight size is designed for Night Sky applications, while both sizes may be utilized in corridor areas for commercial and hospitality applications. This product range is not only commercially qualified, but also reasonably priced, with IP classifications that enable install in both indoors and outdoor areas. The high-powered LED light engine is low-voltage and comes with a range voltage driver, making it easier to fulfill a variety of site requirements.



MEASUREMENTS

DIMENSION	: 9" W x 3.75" H x 4" Ext
BACK PLATE	: 4.75" W x 4.75" H x 2.25" HCO
HANGING WEIGHT	: 3.41 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,400 Rated (1,980 Del.)
BULB	: 2 x 12W LED DC Integrated , 24W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Up&Down

FINISHES OPTION

Black (BK)

White (WT)

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up&Down
RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com