

8WA1 screw terminals

Fuse terminals



	Terminal size
	1.5 mm ²
Terminal width	10 mm
Rated uninterrupted current I _u when using fuses	6.3 A
Rated uninterrupted current I _u when using the isolating link	16 A
Rated insulation voltage U _i when using fuses	250 V
Rated insulation voltage U _i when using the isolating link	800 V
AWG	18 ... 14
AWG	18 ... 14
Connection capacity, rigid	1 ... 2.5 mm ²
Connection capacity, flexible with end sleeve	0.75 ... 1.5 mm ²
Tightening torque	0.8 Nm
Standard	



Version	Color	
For 5 × 25 mm G fuse links		
① Without LED	Beige	8WA1011-1SF12
② With LED 24 V AC/DC	Beige	8WA1011-1SF13
③ With LED 230 V AC/DC	Beige	8WA1011-1SF15
For 6.3 × 32 mm G fuse links (inch fuses)		
① Without LED	Beige	8WA1011-1SF30
② With LED 24 V AC/DC	Beige	8WA1011-1SF31
③ With LED 120 V AC/110 V DC	Beige	8WA1011-1SF32

Special accessories

5 × 25 mm G fuse links				
	Versions	Breaking capacity	Rated uninterrupted current	Article No.
	Quick	Large	1 A	8WA1822-7EF16
			1.6 A	8WA1822-7EF18
			2.5 A	8WA1822-7EF21
			4 A	8WA1822-7EF23
			6.3 A	8WA1822-7EF25
	Slow	Small	1 A	8WA1822-7EF76
			1.6 A	8WA1822-7EF78
			2.5 A	8WA1822-7EF81
			4 A	8WA1822-7EF83
			6.3 A	8WA1822-7EF85
Isolating links, 5 × 25 mm				
	Size		Article No.	
	5 × 25 mm		8WA1891	

See general accessories, page 14/78 onwards