



jalas® CLEAN 3500

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2022 S1, LG

Learn more

COOL AND RIGHT WHEN ONLY WHITE WILL DO

Cool and light safety sandal with toe cap in aluminium created for work in e g laboratories and other places when only white shoes will do. The sandal is also very popular among spray painters. Upper material in PU-coated leather and textile. Outsole in PU. The Ergothan shock absorption system protects back and legs for those who walk a lot.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Breathable
- Excellent shock absorption

FUNCTIONS

- Low weight
- Oil-resistant outsole
- Anti-static properties
- Polstered shaft edge
- Ventilating insole
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF
Toe injuries, Antistatic

PRIMARY ENVIRONMENTS OF USE
Indoors

PRIMARY AREAS OF USE
Laboratory work, Paint spraying work

SPECIFICATION
TYPE Safety footwear, Sandals
CATEGORY Cat. II
FITTING Regular
COLLECTION Clean
UPPER MATERIAL PU-coated leather, Textile
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester, polyamide
INSOLE JALAS 8103 FX2 Pro-X
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in PORON® XRD®
OUTSOLE MATERIAL PU outsole
FASTENING Hook-and-loop
COLOUR White
NET WEIGHT, (SIZE 42) 1.01 kg

COMPLIANCE
CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

EN ISO 20345:2022
S1, LG

FEATURES
- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	3500-36	6408487430985
37	4	5	6	3500-37	6408487430992
38	5	5.5	6.5	3500-38	6408487431005
39	6	6.5	7.5	3500-39	6408487431012
40	6.5	7.5	8.5	3500-40	6408487431029
41	7	8	9	3500-41	6408487431036
42	8	9	10	3500-42	6408487431043
43	9	9.5	11	3500-43	6408487431050
44	10	10.5	11.5	3500-44	6408487431067
45	10.5	11	12.5	3500-45	6408487431074
46	11	12	13	3500-46	6408487431081
47	12	13	14	3500-47	6408487431098

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.