

TAORMINA

4545-VGL

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 13"

Width/Diameter: 45"

Minimum Height: 18"

Maximum Height: 71"

Canopy/Backplate: 5.5"

Hanging Type: 1-3" / 1-6" / 1-12" / 2-18" Stems

Product Weight: 25.3lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Clear Inside Etched

Shade 1 Top Width: 6.5"

Shade 1 Height: 0.25"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 81

Bulb Quantity: 8

Bulb Included: Yes

Wire Length: 120"

Cord Type: B & W TEFLON W/ GROUND WIRE

Dimmer Type: ELV, TRIAC

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 4075

Title 24: No

Field Serviceable: Yes



SHIPPING

Carton 1: 39" x 39" x 19"

Carton 1 Weight: 47lb

Shipping Method: Truck Only

Country of Origin: PH