

Project Name

Location

Prepared By



Notes

(www) 18-17-0025 03-20-07

General

| | |
|---------------------------|-----------------------------|
| Status | Active |
| Fixture Type | Vapor Tight |
| Finish | Gray |
| Wattage | 40W/50W/60W |
| Lumen Output | 5360L-7991L |
| CCT (Kelvin) | 3000K/4000K/5000K |
| Temperature | Soft White to Natural Light |
| IP Rating | IP65 |
| Indoor or Outdoor Fixture | Indoor; Outdoor |

Specifications

| | |
|-----------------------|---------------------------------|
| Technology | LED |
| CRI | 80+ |
| Voltage | 120V-347V |
| Beam Angle | 120 |
| Rated Hours | 50000 |
| Operating Temperature | -40C (-40F) to +45C (+113F) |
| Dimmable | Yes-Dimmable |
| Dimming Note | 0-10V Dimming |
| Lens Material | Polycarbonate (PC) |
| Surge Protection | Built-in surge protection - 2KV |
| Weight (lb.) | 5.07 |
| Material | Polycarbonate (PC) |

Dimensions

| | |
|--------------|-------|
| Height (in.) | 3.54 |
| Width (in.) | 4.84 |
| Length (in.) | 47.24 |

Compliance

| | |
|----------------------|-------------------------------|
| Safety Listing | cETLus - Listed |
| Location Rating | Wet |
| ENERGY STAR | No |
| DLC Approved | Yes |
| DLC ID | S-8XDJS8;S-WP9TSQ |
| NSF Approved | Yes |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| California Prop 65 | Lead |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| Flicker Free | No |
| SDS Sheet | LED_Fixture |

Additional Information

| | |
|------------------------|----------------------------------|
| Additional Information | 90 Minute Battery Backup Runtime |
| Includes | Mounting Hardware |
| Warranty | 5-Years |