



Project / Job Name:

Location:

Fixture Type:

Notes:

65-1300 - 40/30/20 Watt LED 1x4 Center Basket Troffer Retrofit Kit; 35K/4K/5K CCT; Dimmable; 120-277 Volt; Matte White Finish



GENERAL

Company	NUVO
EA Height	3.15
EA Width	11.34
EA Length	49.33
Bulb Included	Integrated
Dimmable Text	0-10V Dimming
Material	Steel
Fixture Type	Troffer
Includes	Mounting Brackets, Wire nuts
Product Notes	Default Wattage setting is 40W
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<20%
Up Down Installation	Down
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	White
Amps	0.333-0.144/0.250-0.108/0.167-0.072A
Lens Finish	Frosted
Lens Material	Polycarbonate (PC)
Power Factor	>0.9
SDS Class	LED_Fixture
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	2 x 32W T8
Incandescent Equivalent	125W

ELECTRICAL

CCT (Kelvin Temp)	3500K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	120
Color Temp	Neutral White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-20C (-4F) to +40C (+104F)
Lumens	5000L/3750L/2500L
Volts	120V-277V
Watts	40W/30W/20W

PHYSICAL

Lamp Base	Integrated
Finish	Matte White
Housing Color	Matte White
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Rectangle

ADDITIONAL INFO

Warranty	5-Years
----------	---------

FEATURES

Flicker Free	Yes
--------------	-----

PACKAGING

UPC	045923411359
Case Cube	1.0197
Case Height	3.15
Case Length	49.33
Case Quantity	1
Case UPC	10045923411356
Case Weight	7.5
Case Width	11.34
EA Cube	1.0197
EA Height	3.15
EA Length	49.33
EA Quantity	1
EA Weight	7.5
EA Width	11.34
Pack Type	Kraft Box
Web Height	2.71
Web Length	47.81
Web Width	11.92

COMPLIANCE

Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
DLC ID	S-DK02XZ
FCC Compliant	Yes
IC Rated	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus - Classified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24 Compliant	No