

SONNY

F2842-BRL

Sonny takes inspiration from a mid-century sputnik chandelier, reimagined with an organic, staggered rhythm. Finished in Bronze Leaf, slender arms extend outward, culminating in a softly glowing cloud seedy glass globe. The seemingly randomized arrangement creates a dynamic, almost celestial composition. Available as a 4-light sconce and a 12- or 20-light chandelier, Sonny serves as a stunning centerpiece for dining or living spaces.

FINISHES

BRONZE LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 20"

Width/Diameter: 41.75"

Minimum Height: 26.75"

Maximum Height: 68.25"

Canopy/Backplate: 6"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 26.4lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Seeded Cloud

Shade 1 Top Width: 5.5"

Shade 1 Height: 5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 12

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 47" x 43" x 26"

Carton 1 Weight: 42lb

Shipping Method: Truck Only

Country of Origin: PH

