

Garant**Micro-adjustable head ER, Connection: ER25****Order data**

Order number	237548 ER25
GTIN	4045197778949
Item class	29W

Description**Version:**

With integral taper. **Simple connection to ER collet chucks.** Adjustment accuracy 0.002 mm on the Ø.

Application:

Best with insert No. 237695 – 237698.

Note:

During the extraction cycle ensure cutting edge orientation $\pm 20^\circ$! Insert toolholder No. 237604 1 for extending the Ø range to 47.9 – 59.1 mm.

Technical description

Reach L_1	65 mm
Connection	ER25
suitable indexable insert	CC..0602..
Insert screw	237606 size 1
Boring range Ø	39.9 - 51.1 mm
Standard	ISO 15488-B
Through-coolant	yes
Type of product	Boring tool

