Tectonic | E30142-BKAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

An enigmatic light source projects from the wall, obscured by two panels with an organic textural relief and split down the center to cast soft ambient light. Open at the top and bottom as well, the light shines both upwards and downwards and signals the source of its illumination through the crevice that it creeps out from. Finished in Matte Black externally, the interior of the sconces are powder coated antique brass to add warmth to the rustic glow. Available in 3 sizes, this ADA compliant sconce series adds mystique to the spaces it's installed.



*Height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION	: 4.75" W x 14" H x 3.75" Ext
BACK PLATE	: 4.75" W x 4.5" H x 2.25" HCO
HANGING WEIGHT	: 3.45 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,280 Rated (480 Del.)
BULB	: 2 x 8W LED AC Integrated , 16W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black / Antique Brass (BKAB)

MATERIAL

Aluminum

RATINGS

Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com