



Project / Job Name:

Location:

Fixture Type:

Notes:

65-896 - 150/125/100 Watt; 3K/4K/5K CCT Large LED Post Top; Bronze; 120-347 Volt



GENERAL

Company	NUVO
EA Height	6.1
EA Width	23.03
EA Length	32.87
Bulb Included	Integrated
Diameter	20.89
Fitter	3
Material	Die-cast Aluminum
Fixture Type	Post Top
Product Notes	Default Wattage: 150W
Status	Active
Surge Protection	Built-in surge protection - 6KV
Total Harmonic Distortion	<20%
Wire Color	Black
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	Bronze
Amps	1.250-0.430/1.040-0.360/0.830-0.290A
Integrated Features	Integrated Photocell
IOT Enabled	No
Lens Finish	Opaque
Lens Material	Polycarbonate (PC)
Lensed	Yes
Photo Cell	Yes - Bypassable
Power Factor	>0.9
SDS Class	LED Fixture
Indoor Outdoor	Outdoor
Product Technology	LED

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	90
Color Temp	Soft White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	+32F to +113F (0C to +45C)
HID Equivalent	225W-300W
Lumens	21750L-12500L
Volts	120V-347V
Watts	150W/125W/100W

PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
Housing Color	Bronze
ANSI Base	Integrated
Lamp Type	Integrated LED

ADDITIONAL INFO

Warranty	5-Years
----------	---------

PACKAGING

UPC	045923653001
Case Cube	2.6723
Case Height	6.1
Case Length	32.87
Case Quantity	1
Case UPC	10045923653008
Case Weight	19.14
Case Width	23.03
EA Cube	2.6723
EA Height	6.1
EA Length	32.87
EA Quantity	1
EA Weight	19.14
EA Width	23.03
Pack Type	Box
Web Height	23.76
Web Width	20.89

COMPLIANCE

Bug Rating	B4-U3-G1
CA Prop 65	Lead
DLC ID	S-KZ0WWW
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cULus
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No