



PRCP2 Lighted Buttons

PrimeChime Plus 2® Buttons

The PrimeChime Plus 2® keeps all the popular features of NICOR's PrimeChime Plus® electronic doorbell with added compatibility with most video doorbell buttons. The PRCP2 combines both line voltage and low voltage into a single unit and offers a paintable, screwless faceplate for simple installation and a seamless look. Separate ring tones for front and rear doors allows you to keep track of exactly which door to answer. NICOR's lighted button makes your doorbell easily visible to visitors at all times of day, welcoming them to your home.

- Decorator Button Finish:** Available in Matte White, Copper, Nickel, and Black
- Stucco Button Finish:** Available in Antique Brass, Polished Brass, Architectural Bronze, Nickel, and Matte White
- Installation:** Decorator button mounts to wall with included screws. Stucco button mounts to wall with included mounting tube and hardware.

Accessories	Accessories sold separately
PRCP2BUTTONDBBK	Lighted Decorative Button - Black
PRCP2BUTTONDBCO	Lighted Decorative Button - Copper
PRCP2BUTTONDBNK	Lighted Decorative Button - Nickel
PRCP2BUTTONDBWH	Lighted Decorative Button - White
PRCP2BUTTONSBAB	Lighted Stucco Button - Antique Brass
PRCP2BUTTONSBBZ	Lighted Stucco Button - Architectural Bronze
PRCP2BUTTONSBPB	Lighted Stucco Button - Polished Brass
PRCP2BUTTONSBNK	Lighted Stucco Button - Nickel
PRCP2BUTTONSBWH	Lighted Stucco Button - White



Lighted Deco Button Lighted Stucco Button



STP

LED Step Light

NICOR's LED Step Lights are a great complement for your residential and commercial projects. This step light not only provides a touch of safety, but it offers a warm, natural glow making it a perfect accent for any project. For a truly customizable choice, this LED step light offers paintable faceplates making them versatile for any application. Wet location approved for indoor and outdoor use.

- CCT:** 2700K
- Reported Lifetime:** 50,000 Hours
- Power Draw:** 1W
- Input Voltage:** 120 VAC
- Operating temperature:** -10° to 122°F (-23°C to 50°C)
- Installation:** Mounts directly in a non-metallic, single gang box.

Accessories	Accessories sold separately
Horizontal	
Horizontal Step Light Faceplate Black	FPHBK (Black)
Horizontal Step Light Faceplate Oil-Rubbed Bronze	FPHOB (Oil-Rubbed Bronze)
Horizontal Step Light Faceplate White	FPHWH (White)
Vertical	
Vertical Step Light Faceplate Black	FPVBK (Black)
Vertical Step Light Faceplate Oil-Rubbed Bronze	FPVOB (Oil-Rubbed Bronze)

Ordering Information			
Series	Version	Voltage	Finish
STP	10 (Version 1)	120	WH (White)

