



PIP® Food Pro EZ-Twist™

Metal Detectable Polyurethane Foam Corded Ear Plugs - 30 NRR / SNR 38

- Metal detectable (blue) recommended for use in the food industry
- Just Insert & Twist! The fastest fitting foam ear plugs
- Shape conforms to most ear canals
- Softest most comfortable cylinder shaped ear plug
- Black PVC cord for convenience and to prevent loss of ear plugs
- NRR 30 protection

Applications

- Food Industry
- Laboratory Applications
- Canning and Recycling
- Catering
- Clean Room
- Pharmaceuticals

Technical Data

Color	Blue
Sizes Available	OS
Packaging	Boxed
Packed	10 Boxes/Case
Case Dimensions (in)	21.37 x 16.38 x 9.62
Case Weight (lbs)	12.50
Country of Origin	Mexico
Hearing Style	Metal Detectable
Ear Plug Material	Polyurethane Foam
Shape	Barrel Push-In
Cord Material	PVC
Box Count	100
EN 352	EN352-2: Earplugs
Certifications	TAA Compliant

Performance Data

NRR Rating (ANSI S3.19-1974)	30
SNR Rating	38
SLC 80	25
SLC 80 Class	Class 4
Attenuation - High Frequency	38
Attenuation - Medium Frequency	36
Attenuation - Low Frequency	34

Care Instructions

These ear plugs are disposable, but when not in use should be kept in clean, dry condition.



SPECIFICATION SHEET

STYLE: 267-HPF610D

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
267-HPF610D	Blue	OS	616314268717		02616314268715