



Standards

- ANSI/TIA-568.3
- TIA-604-FOCIS
- Telcordia GR-326-CORE

Pre-Polished Connectors

900 μ M cable, 10mm cleave length

LC PROclick®

Color	Fiber Type	12-Pack	100-Pack
Aqua	50 μ M, OM3/OM4	① FCLC900K50GM12	FCLC900K50GM100
Beige	62.5 μ M, OM1	FCLC900K62M12	–
Black	50 μ M, OM2	FCLC900K50M12	–
Blue	SM, OS2	FCLC900KSM12	FCLC900KSM100



SC PROclick®

Color	Fiber Type	12-Pack	100-Pack
Aqua	50 μ M, OM3/OM4	FCSC900K50GM12	FCSC900K50GM100
Beige	62.5 μ M, OM1	② FCSC900K62M12	–
Black	50 μ M, OM2	FCSC900K50M12	–
Blue	UPC SM, OS2	FCSC900KSM12	FCSC900KSM100
Green	APC SM, OS2	FCSC900KASM12	–



ST 2Click®

Color	Fiber Type	12-Pack
Aqua	50 μ M, OM3/OM4	FCST50GM12
Beige	62.5 μ M, OM1	FCST62M12
Black	50 μ M, OM2	FCST50M12
Blue	SM, OS2	③ FCSTSM12



PROclick® Fiber Tool Kit

Description

Includes: cleave and strip tools, scissors, pocket visual fault locator, launch cord, adapter insert and bullet, clamp, work mat, cleaning fluid and wipes, safety glasses, case (see page G18 for more detail)

Catalog No.

OFPROKT1

Tools

Description

Fiber Cleavers	Multimode only, score and snap style	OFCLV3
	SM or MM fiber, precision, with case	④ OFCLV5
Visual fault locator (ST, SC, LC); use during termination for optimum test results		⑤ OFVFLKT1




Four Easy Termination Steps



Strip



Wipe



Cleave



Insert and Click

Note: See color chart on page G2. For termination tools and accessories, see page G18. Cleave tool OFCLV3 suitable for multimode only. Visual Fault Locator OFVFLKT1 recommended during termination. Precision cleave tool OFCLV5 required for singlemode terminations. Use precision cleave tool for optimum performance.