Cubist | E21683-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION



MEASUREMENTS

DIMENSION	: 30" W x 2.25" H x 3.5" Ext
MAX OAH	: 2.25" W x 2.25" H
HANGING WEIGHT	: 3.4 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 800 Rated (400 Del.)
BULB	: 1 x 13W LED DC Integrated , 13W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

- Black (BK)
- Gold (GLD)
- Polished Chrome (PC)
- Satin Nickel (SN)

MATERIAL

Aluminum, Acrylic

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Vertical / Hori
RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com