

LARK

B3220-PBR

The Lark sconce exists at the intersection of modern and playful, eye-catching and functional. It establishes its own graphic vernacular with rotating arms bent into arcs and right angles. The two large cylindrical heads can be positioned to direct light as needed. Available in Patina Brass or Bronze finishes, Lark brings character to any space.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 20.25"

Width/Diameter: 21"

Canopy/Backplate: 2.5"

Product Weight: 9.68lb

Extension: 22.5"

Top to Center: 13.75"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: R16 LED

Max Wattage: 15

Bulb Quantity: 2

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Switch Type: ON/OFF SWITCH ON FIXTURE

Gem Box Required (2"x3"): Yes

Dark Sky: No

SHIPPING

Carton 1: 26" x 24" x 7"

Carton 1 Weight: 13lb

Shipping Method: Ground

Country of Origin: VN

