

# Product data sheet

## Characteristics

# QO120PCAFIC

Mini circuit breaker, QO, 20A, 1 pole, 120VAC, 10kA, combo arc fault, plug on neutral, plug in mount, clam pack



### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	PoN combination ARC-fault
Ratings	HACR rated
Electrical Connection	Pressure plate
Connections Terminals	Plug-on neutral
Type of Packing	Clam packaging

### Complementary

Interrupt Rating	10 kA 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper AWG 12...AWG 8 aluminium
Height	4.76 in (121 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.53 lb(US) (0.240 kg)

### Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

### Ordering and shipping details

Category	01318-QO 1 POLE BULK BRKRS.
Discount Schedule	CPQ
GTIN	785901978435
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	4.10 in (10.414 cm)
Package 1 Length	7.00 in (17.78 cm)
Package 1 Weight	8.47 oz (240.0 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	1200
Package 2 Height	45.00 in (114.3 cm)
Package 2 Width	40.00 in (101.6 cm)

Package 2 Length	42.00 in (106.68 cm)
Package 2 Weight	752.00 lb(US) (341.101 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	3
Package 3 Height	8.40 in (21.336 cm)
Package 3 Width	4.00 in (10.16 cm)
Package 3 Length	5.00 in (12.7 cm)
Package 3 Weight	28.48 oz (807.394 g)

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>