Floating | E42046-GLBK


Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION



MEASUREMENTS

DIMENSION	: 30" W x 67" H x 2.25" Ext
HANGING WEIGHT	: 62.48 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 6,000 Rated (1,200 Del.)
BULB	: 1 x 60W LED DC Integrated , 60W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000-4500-6400K

FINISHES OPTION

Gold Leaf / Black (GLBK)

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Damp Location
CA Title 24
ADA

ADDITIONAL

RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com