



Fibre-Metal®

Type I Vented, Industrial Climbing Helmet with PC/ABS Shell, 6-Point Nylon Suspension, Wheel Ratchet Adjustment, Chinstrap and Pre-Installed PC Visor

- Four-point buckle chinstrap for a secure fit and improved adjustability
- Six-point ratchet suspension for excellent impact absorption
- Low profile and balanced weight distribution for increased comfort
- Resistant to extreme temperatures -22° F to +122° F (-30° C to +50° C)
- ABS shell for great impact resistance and durability
- Included certified polycarbonate visor for extra protection

Technical Data

Color	Green, Gray, Multi, Dark Blue, White, Yellow, Orange, Red, Black
Sizes Available	OS
Packaging	Bagged Each
Packed	20/Case
Case Dimensions (in)	22.44 x 17.72 x 19.69
Case Weight (lbs)	30.20
Country of Origin	China
Shell Material	ABS
Shell	Vented
Brim Length	Micro
Size Adjustment	Wheel Ratchet
Suspension	6 Point Polyester
Chin Strap	4-Point Polyester
Certifications	ANSI/ISEA Z89.1, EN 397

Performance Data

ANSI Type	Type I
Electrical Class	Class C

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
FSH11011	Black	OS	883940386201		00883940386911
FSH11071	Dark Blue	OS	883940386232		00883940386942
FSH11009	Gray	OS	883940386195		00883940386904
FSH11004	Green	OS	883940386188		00883940386898
FSH11080	Multi	OS	883940386225		00883940386935
FSH11003	Orange	OS	883940386171		00883940386881
FSH11015	Red	OS	883940386218		00883940386928
FSH11001	White	OS	883940386157		00883940386867
FSH11002	Yellow	OS	883940386164		00883940386874