Aroeve

Model: MK08W

Smart Purifying Fan

User Manual





WORKS WITH amazon alexa

WORKS WITH Google Assistant

Customer Service: support@aroeve.com

PLEASE READ AND SAVE THESE IMPORTANT SAFETY INSTRUCTIONS

US

CONTENTS

SAFETY INSTRUCTIONS ---- 1 - 2

SPECIFICATION ---- 2

GETTING TO KNOW YOUR AIR PURIFIER ---- 3

GETTING STARTED ---- 4

APP SETUP ---- 5 - 7

SMART LIFE APP TROUBLESHOOTING ---- 7 - 8

CONTROL AND DISPLAY ---- 9 - 12

HOW TO USE AROMATHERAPY FUNCTION ---- 13

CLEANING OF COMPLETE MACHINE ---- 13

REMOVAL AND CLEANING OF CIRCULATING FAN ---- 13

DISASSEMBLY AND CLEANING OF SCREEN ---- 14 - 15

TROUBLESHOOTING ---- 15 - 16

WARRANTY ---- 16

SAFETY INSTRUCTIONS

Important:
Please read and comply with all of the instructions and warnings provided in this manual before using the product. Failure to comply with the instructions and warnings provided herein may result in inaccurate results or damage to the product itself.

01. Ensure the plug fits properly into a polarized power outlet.
02. This appliance should only be used in room with temperatures between 40°F and 95°F.
03. To avoid fire or shock hazard, connect the purifier into correct electrical outlet.
04. NEVER place on a soft surface such as a bed or sofa as this could cause the unit to tip over and the air inlet or outlet grills to be blocked.
05. Do not place anything on top of unit.
06. Do not move or tilt the unit while it is in operation.
07. Do not insert fingers or objects into the air inlet and air outlet.
08. Do not use outdoors.This unit is only suitable for indoor use, please avoid strong sunlight and rain.
09. Do not use near water to avoid electrical hazards.
10. Do not use the unit in wet or humid environments.
11. Do not handle the unit with wet hands.Thoroughly dry your hands before handling any part of the air purifier.
12. Do not place the unit directly below an air conditioner to prevent any moisture from getting in to the purifier.
13. Do not allow children,pet to play on or near the unit. Close supervision is necessary when any appliance is used by or near children, or disabled persons.
14. Keep unit away from heated surfaces and naked flames such as stove tops,ovens, raditors or computers.
15. Always turn the purifier off before unplugging it.
16. Always unplug the air purifier before moving or cleaning the unit, opening the rear cover, changing the filter and whenever the unit is not in use.
17. To disconnect the unit, be sure to pull the plug instead of the cord.
18. This unit does not remove carbon monoxide or radon.It can not be used as a safety device to prevent or clean up accidents with combustion processes and hazardous chemicals.
19. NEVER use detergents,gasoline,glass purifier,furniture polish,paint thinner,or other household solvents to clean any part of the purifier.
20. Non-professional personnel or unauthorized repair personnel shall not repair or transform the machine by themselves.
21. Do not operate the appliance with a damaged cord or plug. If the motor fan fails to operate or the unit has been dropped or damaged in any manner, contact the customer service.
22. Always allow 15 inches of clearance on all sides of the purifier.
23. This product complies with the maximum allowable concentration of ozone of 0.050 parts per million by volume (ppmv) in a 24-h period.

Warn the user to unplug or disconnect the appliance from the power supply before servicing.
To Reduce The Risk Of Fire, Electric Shock Or Injury To Persons, Do Not Use
Replacement Parts That Have Not Been Recommended By The Manufacturer (e.g. Parts Made At Home Using A 3D Printer).

SAFETY INSTRUCTIONS

To reduce the risk of electric shock, this equipment has a polarized plug (one blade is wider than the other). This plug will fit in a polarized outlet only one way. If the plug does not fit fully in the outlet, reverse the plug. If it still does not fit, contact qualified personnel to install the proper outlet. Do not alter the plug in any way .

Warning: Any changes or modifications to this unit not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

This appliance has a polarized plug (one blade is wider than the other). To reduce the risk of electric shock, this plug is intended to fit in a polarized outlet only one way. If the plug does not fit fully in the outlet, reverse the plug. If it still does not fit, contact a qualified electrician. Do not attempt to defeat this safety feature。


WARNING：To Reduce The Risk Of Fire Or Electric Shock, Do Not Use This Fan With Any Solid-State Speed Control Device.


NOTE: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:
—Reorient or relocate the receiving antenna.
—Increase the separation between the equipment and receiver.
—Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
—Consult the dealer or an experienced radio/TV technician for help.

SPECIFICATION

Name：Smart Purifying Fan	Rated Frequency : 60Hz
Rated Voltage : 120V~	Rated Power : 53W
Rated Current : 0.68A	

GETTING TO KNOW YOUR AIR PURIFIER





PACKAGE CONTENTS




1 X
Smart Purifying fan



1 X
User Manual



1 X
app download and installation guide



1 X
Original essential oil pads (Complimentary 5 pads)



1 X
True HEPA Original Filter (Pre-Installed)




1 X
Washable primary filter screen



3 X
Circulating fan replacement screw


GETTING STARTED

1





Your air purifier comes with an original filter included. Before use, do remember to remove the packaging from the filter.

1. Place the air purifier on a flat, stable surface like the floor. Open and remove the air intake grille on the back of the machine. (See picture 1)
2. Tear open the filter bag and remove the HEPA filters. (See picture 2)
3. Find the water wash strainer in the packing box and assemble it according to this figure(See picture 3)
4. Combine the filters and insert them into the machine. Close the grill to use. (See picture 4)




2






3



4




NOTE:
Ensure that the True HEPA filter (the side with the ribbon handle) is facing outward when installing the filter.

APP SETUP

1. Download Smart Life APP

To download the Smart Life Smart app, scan the QR code or search "Smart Life" in the Apple App Store® or Google Play Store.

2. Open the Smart Life Smart app. Log In or Sign Up.



(Sign Up) (Log In)


3. Ensure that the phone is connected to Wi-Fi, open the APP interface, and enable the Wi-Fi pairing function of the product at the same time (please refer to page 6 for product Wi-Fi pairing). Follow the following steps for product pairing.


APP SETUP


Step 1:
click "+"to Add Device

Step 2:
Manual Add Device, click "Air Purifier(Wi-Fi)"

Step 3:
Enter your Wi-Fi password and click "Next"







SETUP TIPS:


1. Ensure that you are connected to a secure 2.4GHz Wi-Fi network during setup. Do not use a 5GHz network as it will not successful pairing.
2. Complete pairing within 3 minutes. If the network distribution fails within this time, the Wi-Fi indicator light will go out. To restart, long press the " ⊛ " button for 3 seconds.
3. In pairing mode, after a power outage, the Wi-Fi pairing mode is disabled. To re-enter pairing mode, press the " ⊛ " button for 3 seconds. The Wi-Fi indicator light will turn on again.


APP SETUP


Step 4:
To confirm that the product is powered on, please follow the operation instructions, and long press " " to enable Wi-Fi matching, and ensure that the Wi-Fi indicator blinks.
(Choose the Blink Slowly)

Step 5:
Open the search product, enter the matching moment

Step 6:
The pairing is successful, and the operation mode of the smart APP is enabled







SMART LIFE APP TROUBLESHOOTING

My smart air purifier isn't connecting to the Smart Life app.

1. During the setup process, you must be on a secure 2.4GHz Wi-Fi network. (Please do not use the 5G network, otherwise, the pairing cannot be successful.)
2. Confirm that the network is working correctly.
3. Make sure the Wi-Fi password you entered is correct.

TIPS:

① There should be no spaces at the beginning or end of the password.
② Test the password by connecting a different electronic device to the router.
③ If you're manually typing in the SSID and password, double check that both are entered correctly.

SMART LIFE APP TROUBLESHOOTING

4. Try moving your air purifier closer to the router.Your phone should be as close as possible to your air purifier.
5. Your router may need to be at a higher location, away from obstructions.
6. Make sure your air purifier and router are away from appliances (such as microwave ovens, refrigerators, electronic devices, etc.) to avoid signal interference.
7. If you're using a VPN, make sure it's turned off while setting up your air purifier.
8. Disable portal authentication for your Wi-Fi network.

NOTE:

If portal authentication is enabled, the air purifier will not be able to access your Wi-Fi network, and setup will fail.

My air purifier is offline.

1. Make sure the air purifier is plugged in and has power, then refresh the Smart Life menu by swiping down on the screen.
2. Make sure your router is connected to the internet and your phone's network connection is working.
3. Delete the offline air purifier from the Smart Life app. Long press and click Delete. Reconfigure the air purifier with the Smart Life app.

NOTE:

Power outages, internet outages, or changing Wi-Fi routers will cause the air purifier to go offline.

CONTROL AND DISPLAY

Speed Button		Sleep wind speed indicator
	L	Low wind speed indicator
	H	High wind speed indicator
	T	Turbo wind speed indicator (App wake-up only)
Mode&WIFI Button		Manual gear: Fan mode indicator
		Manual gear: Air purifier indicator
		Manual gear: Purifying fan indicator light
		Automatic gear: Auto mode indicator
	ECO	Automatic gear: Eco mode indicator
		WI-FI indicator (Press for 3s to turn on)
OSC Button		Left-right oscillation indicator
		Up-down oscillation indicator
		3D oscillation indicator
Light/Lock Button		Atmosphere indicator light
		Child lock indicator (Press for 3s to turn on)
Filter Button	%	The remaining life of the filter is displayed
	HEPA	If the indicator light starts blinking, it means that the filter needs to be replaced. After replacing the filter, press and hold the button for 3 seconds to reset.
Air Info Button	PM10	The quantity of PM10 particles can be queried
	PM2.5	The quantity of PM2.5 particles can be queried
	PM1.0	The quantity of PM1.0 particles can be queried
		Air quality display light Air quality can be displayed in real time, and four colors represent four states.

CONTROL AND DISPLAY

NOTE:

1. Install the filter as required, and connect it to the power supply
2. When the product is powered on for the first time, the PM2.5 sensor in the machine will wake up, and the corresponding display light will also turn on synchronously. After the preheating is completed, the prompt sound of "drip" will be heard before the machine can be operated

1. " ⏻ " ON/OFF Button

- Tap " ⏻ " to turn on the purifier. The fan will start working in automatic mode, and the 3D shake head function will be enabled. At this point, the sensor begins to identify the surrounding air quality, and the corresponding air quality will be displayed on the screen.
- Tap " ⏻ " again to turn off the purifier.

2. " ⊞ " Mode Button

Tap " ⊞ " to switch between auto mode.ECO mode.fan mode.purifier mode and purifying fan mode.Hold down for 3 seconds to enable wifi pairing.

● About Auto mode

Auto mode uses a smart laser dust sensor to adjust fan speed automatically based on air quality.

For example, if the air quality is bad, the fan will automatically set to a turbo speed. See the figure below for details.

Air Quality indicator Chat		
Indicator Color	**Air Quality**	**Auto Mode Fan Speed**
Blue	Very Good	Sleep Mode
Green	Good	Low
Orange	Moderate	High
Red	Bad	Turbo

NOTE: In auto mode, the purifier starts synchronously with the fan by default, and the wind speed cannot be set.

● About ECO mode

ECO mode is highly energy-efficient compared to auto mode. In ECO mode, if the sensor detects continuous good air quality for 30 minutes, the machine will enter standby mode and stop operating. When the sensor detects poor air quality in standby mode, the machine will resume operation.

● About fan mode

In fan mode, only the fan function is enabled. In this case, you can adjust the wind speed by pressing the wind speed button.

● About purifier mode

In purification mode, the product activates the purification function only, allowing you to adjust the wind speed based on the actual conditions by pressing the speed button.

CONTROL AND DISPLAY

NOTE:
In purification mode, for optimal purification efficiency, the fan will automatically return to a parallel position, and the oscillation function cannot be operated at this time.

● **About purifying fan mode**

In the purifying fan mode, the fan function is enabled, and the wind speed can be adjusted by pressing the wind speed button according to the actual situation

● **About Wi-Fi pairing**

long press the " " button for 3 seconds, Wi-Fi indicator will start flashing, the product will enter the network distribution mode, open the APP at the same time, click Add device to start pairing (please check the following APP Setup for pairing steps)

NOTE:

Indicator lights flashing:pairing is underway
Indicator Steady on:The pairing is successful
Indicator off:Pairing fails

TIPS:

1. During the setup process, you must be on a secure 2.4GHz Wi-Fi network. Confirm that the network is working correctly.(Please do not use the 5G network, otherwise, the pairing cannot be successful.)
2. Please complete the pairing within 3 minutes. If the network distribution fails within 3 minutes, the Wi-Fi indicator light will go out, and then stop the network distribution. Long press the timing button for 3 seconds to restart the network distribution mode.
3. Turn off the wifi function, Long press the timing button for 3 seconds to restart the network pairing mode. In pairing mode, when the machine restarts after a powerd outage, Wi-Fi pairing mode is disabled.

3. " " Speed Button

Choose the wind speed button, you can freely switch between sleep gear, L gear, H gear; Choose the right wind speed

NOTE:

The wind speed button can be adjusted only in manual mode, which includes purifying mode, fan mode, and purifying fan mode

TIPS:

1. If you need to enable super turbo wind speed, you can do so on the app.
2. In sleep mode, the screen slackens for a better experience.

4. " " Osc Button


Tap the " " button to select 3D all-round shake, or open the left and right shake, or up and down shake.

NOTE:

In the purification mode, the state with the optimal purification efficiency is considered, so the shake head function cannot be enabled

TIPS:

If you need to set the shaking Angle, you can set it in the app.



CONTROL AND DISPLAY

"This product employs overload protection (fuse). A blown fuse indicates an overload or short-circuit situation. If the fuse blows, unplug the product from the outlet. Replace the fuse as per the user servicing instructions (follow product marking for proper fuse rating) and check the product. If the replacement fuse blows, a short-circuit may be present and the product should be discarded or returned to an authorized service facility for examination and/or repair."

5. " " Light/Lock Button

Tap the " "button, you can open the night atmosphere lamp, at the same time long press 3 seconds can open the child lock function, in case of children's misoperation.

TIPS:

If you need to adjust the brightness of the atmosphere lamp and change it, you can go to the Settings in the APP.

6. " " Filter Button

1. Tap the " " button to query the remaining life of the filter. If the service life is too low, the HEPA indicator lights on, indicating that the filter needs to be replaced.

   TIPS:

   Strainers can be purchased at the official AROEVE flagship store
2. After replacing the filter screen, long press the " " button for 3 seconds, the reset is successful, the HEPA indicator stops blinking, and 5 seconds later it goes out and returns to the main page.

7. " " Air Info Button

Tap the " " button, you can query the value of particulate matter under different diameters (PM10,PM2.5,PM1.0);

TIPS:

Generally, the lower the value, the better the air quality.

8. Memory function

Built-in memory function, normal shutdown can remember the mode, wind speed, shaking head, lamp;

NOTE: that the child lock and timing function does not carry on memory.

9. Timing function

This function can be set on the APP.

10. Shutdown correction

The product has the function of automatic correction when the machine is shut down. When the machine is shut down, the shaking head will continue to work, and a countdown will appear on the display screen. When the countdown is over, the machine will return to the original parallel state


HOW TO USE AROMATHERAPY FUNCTION

● **How To Use**

1. Push to open
2. Add a few drops of the essential oils and close the chamber.

NOTES:


1. Shut off the machine before adding the essential oils.
2. Only use the droppers come with the essential oils, do not pour in directly.
3. Add 4-5 drops each time.




CLEANING OF COMPLETE MACHINE

Make sure that the machine is in the state of power off before cleaning

1. it is recommended to use a vacuum cleaner to remove the dust on the surface
2. Use a clean and semi-humid soft cloth to wipe the stained part of the fuselage clean
   Do not use any chemicals or corrosive agents to wipe





REMOVAL AND CLEANING OF CIRCULATING FAN

Please note: For your safety, make sure that the machine can be disassembled and cleaned only when the power is off


1. Aim the Phillips screwdriver at the position of the screw to remove it. If the screw is lost carelessly, there are 3 replacement screws in the packing box for use.
2. Hold the raised parts at both ends of the grille, rotate clockwise to remove the grille, and the grille part can be washed
3. Turn the nut at the front end of the fan blade clockwise to remove the fan blade for washing


Please note: Only three parts, namely grille, nut and fan blade, can be cleaned. After cleaning, they should be dried and assembled according to the following steps

1. Put the fan blade back into the motor shaft and fasten the nut counterclockwise
2. Find the lock icon above the air outlet grille, align it with the convex point on the machine, and fix it in accordance with the direction of the lock
3. Align the screw with the bottom and tighten it counterclockwise.

Ensure that the fan is switched off from the supply mains before removing the guard.
Warn the user to unplug or disconnect the appliance from the power supply before servicing

REMOVAL AND CLEANING OF CIRCULATING FAN






NOTE:
When installing the front grill of the fan, align the lock with the protrusion on the top. Rotate clockwise to open and counterclockwise to lock tightly.

DISASSEMBLY AND CLEANING OF SCREEN

To ensure that the filter can be used for a long time, follow the following steps to clean and maintain the filter:
It is recommended to check the state of the washable filter screen every half a month. If it is found that there is much filter dust, it is recommended to clean it. The cleaning method is as follows:
1. Take out the strainer component and check the state of the outermost washing strainer
2. Tear the strainer along the Velcro interface
3. Wash, clean, and dry
Please note: After drying, it can continue to use. Please according to the installation instructions mentioned before assembly.
TIP: After repeated use of the wash screen 3 times, it is recommended to replace the wash screen with a new one. Please visit Aroeve's official website to purchase.

About the HEPA filter
The service life of the HEPA filter is 3000h. If you need to replace the filter, please visit Aroeve's official website to purchase it.

DISASSEMBLY AND CLEANING OF SCREEN



TROUBLESHOOTING

Problem	Possible Solution
The air purifier makes an unusual noise and the outlet air is less.	Make sure the filter is properly in place with plastic packaging removed.
	Make sure the air purifier is operating on a hard, flat, even surface.
	Replace the filter.
	The air purifier may be damaged, or a foreign object may be inside. Stop using the air purifier and contact Customer Support . Do not try to repair the air purifier
Strange smell coming from the purifier.	Replace the filter element
	Make sure not to use your purifier in an area with high humidity or while diffusing essential oils.
	Contact Customer Support.

TROUBLESHOOTING

Problem	Possible Solution
Filter uses less than 3000 hours the environment light has been on red prompt to replace the filter.	Tip 1: The service life of the filter depends on the environment, if the environment is heavily polluted or dusty, the filter is easy to accumulate dust and becomes dirty. (Note: the environment with greater ventilation is more likely to accumulate dust) Tip 2: Humid weather air will be a little more small molecules, more easily combined with dust to form pm 2.5 particles, the sensor senses pm2.5 particles after the red light will be on. Measures 1: It may be necessary to replace the filter. Check whether the filter has been very dirty and needs to be replaced. Measures 2: The room humidity of 75% or more or opening the window on a rainy day, will continue for 1~2 days with red light until the ambient humidity drops to below 75%.

If your problem is not listed , please contact Customer Support.

WARRANTY

We appreciate your feedback and will do our best guarantee your satisfaction.

Within 2 year after your purchase,shall the product has defects, we will provide a refund or resend you a new one. Please email us with your concern and order number. Your inquiries will be taken care of as soon as possible.

This warranty only cover orders from authorized brand online stores and our official website. We are not responsible for any purchases from other distribution channels.

Contact Customer Support Team:

Email: support@aroeve.com

Aroeve

Contact us:
Email: support@aroeve.com