

SHIVONNE

H1109805-AGB

Paying homage to the modernist designs of Adolf Loos, the soft materiality of Shivonne creates a poetic statement piece. This ethereal chandelier features an ivory linen shade that loosely drapes like a skirt as it envelops a 3- or 5-light candle cluster. An Aged Brass finish on the frame adds to the vintage character, while a fabric-covered cord maintains a sense of cohesion with the shade.

FINISHES

AGED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 15.5"

Width/Diameter: 34"

Minimum Height: 18.75"

Maximum Height: 55.75"

Canopy/Backplate: 6"

Hanging Type: 1-3" / 1-6" / 1-12" / 1-18" Stems

Product Weight: 8lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Textile

Shade 1 Finish: Ivory Linen

Shade 1 Top Width: 34"

Shade 1 Height: 12.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 5

Wire Length: 120"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 31" x 31" x 20"

Carton 1 Weight: 22lb

Shipping Method: Ground

Country of Origin: VN

