

A comfortable, soft glove knitted with a mix of Merino wool and nylon. Food approved.

TEGERA® 4640R

Learn more

WARM AND THIN WITH TOUCHSCREEN FUNCTION

A warm, thin, and comfortable textile glove with touchscreen functionality and approved for food handling. 15 gg knitted with a mix of Merino wool and nylon, without any seams. Perfect to wear inside other gloves for extra warmth when working in cold environments. Each pair retail packed with descriptive hangtag to help customers with their in-store choice.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Comfortable
- Warm
- Breathable

FUNCTIONS

- Approved for handling foodstuffs
- For touchscreen
- Soft
- Thin

MERINO

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF
Contact with cold

PRIMARY ENVIRONMENTS OF USE
Dry environments, Cold environments

PRIMARY AREAS OF USE
Airport work, Building and construction, Food handling, Security- and police work, Transport work, Warehouse work

PRIMARY INDUSTRIES OF USE
Agriculture, forestry and fishing, Food and beverage processing, Transportation and logistics, Warehousing

TYPE OF WORK
Medium weight

SPECIFICATION
TYPE Cold insulation gloves, Textile gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 15
LINING MATERIAL Merino Wool, Nylon, Seamless, Spandex
LENGTH 195-250 mm
DEXTERITY 5
COLOUR Black
PAIRS PER: BUNDLE/CARTON 12/60
DISPLAY TYPE Hangtag with euro slot
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
OUTER MATERIAL SPECIFICATION Nylon, Merino wool, Elastane

COMPLIANCE
CE Cat. II
EAC TP TC 019:2011
EN ISO 21420:2020
EN 388:2016+A1:2018 214XX

FEATURES
For touchscreen
Warm lining

SIZE		ARTICLE NUMBER	EAN
6	XS	4640R-6	7340118365930
7	S	4640R-7	7340118366029
8	M	4640R-8	7340118366111
9	L	4640R-9	7340118366203
10	XL	4640R-10	7340118366296
11	XXL	4640R-11	7340118366388

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.