SATCO | NUVO

Project / Job Name:

Location:

Fixture Type:

Notes:



**62-8087** - Maverick; 44-Inch LED Vanity; 28 Watt; 3000K/4000K/5000K CCT Selectable; Smoked Graphite; Dark Brown Faux Leather

DAMP LOCATION | 90+ CRI | DIMMABLE | ETL US | FC | RoHS COMPLIANT | CCT SELECTABLE | 30,000 HOURS | 3 YEAR WARRANTY | 120-277V

## GENERAL

| | |
|---|---|
| Company | NUVO |
| EA Height | 6.88 |
| EA Width | 6.3 |
| EA Length | 45.7 |
| Mounting Height | 0.75 |
| Bulb Included | Integrated |
| Extends (in) | 4.0 |
| Material | Aluminum / Steel |
| Includes | Mounting Strap/Anchors |
| Status | Active |
| Style | Modern and Contemporary |
| Surge Protection | Built-in surge protection - 2KV |
| Total Harmonic Distortion | 45% |
| Top To Outlet | 8.0 |
| Up Down Installation | Universal |
| CCT Selectable | Yes |
| Wattage Selectable | No |
| Collection | Maverick |
| Finish Family | Gray |
| Amps | 0.230A |
| Lens Finish | Opal |
| Lens Material | Glass |
| Lensed | Yes |
| Power Factor | >0.9 |
| Indoor Outdoor | Indoor |
| Product Technology | LED |
| Fluor Equiv | 60W |
| Incandescent Equivalent | 200W |
| Serviceable Battery | No |
| Battery Indicator | No |
| Digital Display | No |

## ELECTRICAL

| | |
|---|---|
| CCT (Kelvin Temp) | 3000K/4000K/5000K |
| Dimmable | Yes-Dimmable |
| Hours Rated | 30000 |
| Beam Angle (degree) | 120 |
| Color Temp | Soft White to Natural Light |
| CRI | 90+ |
| Dimming Type | Phase cut |
| Operating Frequency | 60Hz |
| Operating Temp | -14F to +104F (-10C to +40C) |
| Lumens | 2520L |
| Volts | 120V-277V |
| Watts | 28W |
| Connection | Hardwire |

## PHYSICAL

| | |
|---|---|
| Lamp Base | Integrated |
| Finish | Smoked Graphite |
| Housing Color | Smoked Graphite |
| ANSI Base | Integrated |
| Lamp Type | Integrated LED |
| Fixture Shape | Cylinder |

## ADDITIONAL INFO

| | |
|---|---|
| Warranty | 3-Years |
| Rated For Enclosed Fixture | No |

## FEATURES

| | |
|---|---|
| Flicker Free | Yes |

## PACKAGING

| | |
|---|---|
| UPC | 045923417214 |
| Case Cube | 5.1448 |
| Case Height | 14.57 |
| Case Length | 46.26 |
| Case Quantity | 4 |
| Case UPC | 10045923417211 |
| Case Weight | 39.38 |
| Case Width | 13.19 |
| EA Cube | 1.1463 |
| EA Height | 6.88 |
| EA Length | 45.7 |
| EA Quantity | 1 |
| EA Weight | 9.02 |
| EA Width | 6.3 |
| Pack Type | Kraft Box |
| Web Height | 5.0 |
| Web Width | 44.0 |

## COMPLIANCE

| | |
|---|---|
| ADA Compliant | Yes |
| Air Tight | No |
| CA Prop 65 | Lead |
| Dark Sky Rated | No |
| FCC Compliant | Yes |
| IC Rated | No |
| Location Rating | Damp |
| NSF Approved | No |
| ROHS Compliant | Yes |
| Safety Listing | cETLus |
| California Ban | Lawful for sale |
| Energy Star Certified | No |
| Title 20 | Exempt |
| T24/JA8 Compliant | No |



© Satco Products, Inc.
All rights reserved 2026