

Straight Blade Devices, Male Plug, Nylon, 4-Position, Heavy Duty, Industrial/Commercial Grade, Angled, 3-Pole 4-Wire Grounding, 50A 125/250V, 14-50P.

By Hubbell Wiring Device-Kellems
Catalog # [HBL9452C](#)

Straight Blade Devices, Male Plug, Nylon, 4-Position, Heavy Duty, Industrial/Commercial Grade, Angled, 3-Pole 4-Wire Grounding, 50A 125/250V, 14-50P, Black, Single Pack.

Features

- Material & Construction: Crafted from industrial-grade nylon, this durable plug withstands daily use, ensuring long-lasting, reliable performance essential for EV charging system integrity.
- Configuration: Includes a 4-position, angled layout with 3 poles and 4 wires, grounding included. It meets EV charging's high demands and boosts safety by reducing electrical hazards.
- Electrical Rating: Boasting a 50A, 125/250V capacity, this plug is suited for high-powered EV charging stations, ensuring efficient and reliable power delivery.
- Safety Compliance: This plug meets strict safety standards with a grounding pin and heavy-duty materials, reducing electrical shock risks and ensuring a secure connection to protect equipment and users.
- Ease of Use: Designed with an angled interface and ergonomic handle, this plug allows easy operation and handling in tight spaces, ensuring safe and effortless insertion and removal.
- Long-Term Reliability: Investing in Hubbell's Straight Blade Male Plug means choosing a product that will not only meet the current demands of EV charging but also continue to deliver performance and safety long into the future.

Specifications

Buy American Compliant	Yes
Nema Rating	14-50P
Buy America(n) Qualified	• Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280

Conductor

Number Of Wires	4-Wire
Number Of Poles	3-Pole

Current



Amperage Rating	50 A
Voltage Rating Description	125/250 V
Dielectric Strength	Withstands 2,000V minimum
Current Rating	50 A
Voltage Rating	• 125 V • 250 V
Current / Amperage Rating	50 A

Dimensions

Length	4.5 in
Weight	0.8 lb.
Height	2.37 in
Width	3.38 in
Dimensions	4.5 in x 3.38 in x 2.37 in

General

Color	Black
Style	Grounding
Cord Range	0.625"-1.310"
Series	Extra Heavy Duty
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585015330
Type	Plug
Material	Nylon

Logistics

Pallet Quantity	765
Carton Quantity	5

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	3

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)