

Fortress®

Lineset duct and fittings.

SUBMITTAL

Contractor:

Job Name:

Date:

Color:

☐ White

☐ Ivory

☐ Brown

☐ Gray

MODEL	SIZE	DESCRIPTION	WHITE	IVORY	BROWN	GRAY	QTY
 LD92	3½	Ducting	84004 (LD92W)	84024 (LD92I)	84064 (LD92B)	84044 (LD92G)	
LD122	4½	Ducting	84104 (LD122W)	84124 (LD122I)	84164 (LD122B)	84144 (LD122G)	
LAD150W	6	Ducting	84180 (LAD150W)				
 LJ92	3½	Coupler	84010 (LJ92W)	84030 (LJ92I)	84270 (LJ92B)	84250 (LJ92G)	
LJ122	4½	Coupler	84110 (LJ122W)	84130 (LJ122I)	84370 (LJ122B)	84350 (LJ122G)	
LAJ150W	6	Coupler	84185 (LAJ150W)				
 LW92	3½	Wall Inlet	84016 (LW92W)	84036 (LW92I)	84276 (LW92B)	84256 (LW92G)	
LW122	4½	Wall Inlet	84116 (LW122W)	84136 (LW122I)	84376 (LW122B)	84356 (LW122G)	
LAW150W	6	Wall Inlet	84189 (LAW150W)				
 LEN92	3½	End Fitting	84007 (LEN92W)	84027 (LEN92I)	84267 (LEN92B)	84247 (LEN92G)	
LEN122	4½	End Fitting	84107 (LEN122W)	84127 (LEN122I)	84367 (LEN122B)	84347 (LEN122G)	
LAE150W	6	End Fitting	84184 (LAE150W)				
 LK92	3½	90° Flat Ell	84011 (LK92W)	84031 (LK92I)	84271 (LK92B)	84251 (LK92G)	
LK122	4½	90° Flat Ell	84111 (LK122W)	84131 (LK122I)	84371 (LK122B)	84351 (LK122G)	
LAK150W	6	90° Flat Ell	84186 (LAK150W)				
 LP92	3½	Soffit Inlet	84014 (LP92W)	84034 (LP92I)	84274 (LP92B)	84254 (LP92G)	
LP122	4½	Soffit Inlet	84114 (LP122W)	84134 (LP122I)	84374 (LP122B)	84354 (LP122G)	
LHJK150W	6	Soffit Inlet	84187 (LHJK150W)				
 LKF92	3½	45° Flat Ell	84012 (LKF92W)	84032 (LKF92I)	84272 (LKF92B)	84252 (LKF92G)	
LKF122	4½	45° Flat Ell	84112 (LKF122W)	84132 (LKF122I)	84372 (LKF122B)	84352 (LKF122G)	
 LCI92	3½	90° Inside Vertical Ell	84002 (LCI92W)	84022 (LCI92I)	84262 (LCI92B)	84242 (LCI92G)	
LCI122	4½	90° Inside Vertical Ell	84102 (LCI122W)	84122 (LCI122I)	84362 (LCI122B)	84342 (LCI122G)	
LAC150W	6	90° Inside Vertical Ell	84183 (LAC150W)				
 LCO92	3½	90° Outside Vertical Ell	84003 (LCO92W)	84023 (LCO92I)	84263 (LCO92B)	84243 (LCO92G)	
LCO122	4½	90° Outside Vertical Ell	84103 (LCO122W)	84123 (LCO122I)	84363 (LCO122B)	84343 (LCO122G)	
 LACM150W	6	120° Adjustable Vertical Ell	84182 (LACM150W)				
LAKM150W	6	120° Adjustable Flat Ell	84181 (LAKM150W)				
 LCFI92	3½	45° Inside Vertical Ell	84000 (LCFI92W)	84020 (LCFI92I)	84260 (LCFI92B)	84240 (LCFI92G)	
LCFI122	4½	45° Inside Vertical Ell	84100 (LCFI122W)	84120 (LCFI122I)	84360 (LCFI122B)	84340 (LCFI122G)	
 LCFO92	3½	45° Outside Vertical Ell	84001 (LCFO92W)	84021 (LCFO92I)	84261 (LCFO92B)	84241 (LCFO92G)	
LCFO122	4½	45° Outside Vertical Ell	84101 (LCFO122W)	84121 (LCFO122I)	84361 (LCFO122B)	84341 (LCFO122G)	
 LT92	3½	Tee	84015 (LT92W)	84035 (LT92I)	84275 (LT92B)	84255 (LT92G)	
LT122	4½	Tee	84115 (LT122W)	84135 (LT122I)	84375 (LT122B)	84355 (LT122G)	
LATK150W	6	Tee	84188 (LATK150W)				
 LDR12292	3½ – 4½	Reducer	84106 (LDR12292W)	84126 (LDR12292I)	84366 (LDR12292B)	84346 (LDR12292G)	

A full-page view of a blank sheet of graph paper. The page is covered by a uniform grid of thin, light gray lines forming small squares. A thicker black border frames the entire grid area.