

# LEGACY

F4236-FOR

A refined take on the classic hurricane lamp, Legacy pairs gracefully curved arms with a rich wrought iron finish. Clear glass shades are etched on the inside to create a translucency that softens the light. Antique-inspired tail details add a touch of historic charm. Available as a 1- or 2-light sconce and a 5-light chandelier, Legacy brings timeless elegance to interiors.

## FINISHES

### FORGED IRON

Coastal Suitable Finish (EPM): No

## DIMENSIONS

Height: 22"

Width/Diameter: 36"

Minimum Height: 26.5"

Maximum Height: 95.25"

Canopy/Backplate: 6"

Hanging Type: 72" Chain

Product Weight: 17lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

## Shade

Shade 1: Glass

Shade 1 Finish: Clear Etched

Shade 1 Top Width: 2"

Shade 1 Bottom L/W: 0" / 3.75"

Shade 1 Height: 12.5"

## ELECTRICAL



### Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 5

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND  
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

## SHIPPING

Carton 1: 40" x 40" x 26"

Carton 1 Weight: 31lb

Shipping Method: Truck Only

Country of Origin: PH

