



Technical Data

Color	Gray
Sizes Available	OS
Packaging	Bagged Pair
Packed	200/Case
Case Dimensions (in)	23.20 x 14.70 x 23.20
Case Weight (lbs)	18.30
Country of Origin	Taiwan
Lens	Tinted
Frame Style	Rimless
Lens Color	Gray
Lens Coating	, Anti-Scratch
Bridge	Molded
Certifications	ANSI Z87.1, CSA Z94.3 Certified, TAA Compliant

UVEX® A700

Rimless Gray Lens, Anti-Scratch Hardcoat

- Affordably priced for all of your work environments
- Aggressive styling provides a stylish fit for your everyday wearer
- Slim sizing fits small or narrow facial profiles
- Lightweight design, flexible temples and soft temple tip pads provide a secure, wraparound fit and all-day comfort
- Molded universal nose bridge provides a comfortable fit
- All lenses provide 99.9% UV protection
- Meets ANSI Z87.1+
- Meets CSA Z94.3

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
A701	Gray	Tinted	Gray	AS	040025108534	70040025108535	70040025108533

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
A701	Gray	Tinted	Gray	AS	040025108534	70040025108535	70040025108533

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated