

Project Name

Location

Prepared By



NUVO 62-1057

40W/LED/5"X48"/FLUSH/3K/WH

Notes

[www] 03-22-2021 04:50:53

General

Status	Active
Fixture Type	BLINK Plus
Finish	White
Wattage	40
Lumen Output	2800
CCT (Kelvin)	3000
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
Color Temperature	Warm White
CRI	90+
Voltage	120V/277V
Rated Hours	50000
Operating Temperature	-17C (+1.4F) to a maximum of +45C (+113F)
Dimmable	Yes - Dimmable - 120V only
Weight (lb.)	5.23
Material	Aluminum

Dimensions

Height (in.)	0.75
Width (in.)	5.50
Length (in.)	48.00

Compliance

Safety Listing	cETLus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2291408
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------