



Technical Data

Color	Green
Sizes Available	14"-18"
Packaging	Bulk Pack
Packed	72 Pair/Case
Case Dimensions (in)	17.32 x 14.57 x 17.32
Case Weight (lbs)	11.46
Clothing Type	Sleeves
Fabric	Cotton, Twill
Weight	9oz
Certifications	ASTM D6413, TAA Compliant
Product Circularity	Reusable / Launderable

Care Instructions



Machine
Wash



Water Temp
60°C



Do Not
Bleach



Tumble Dry



Low Heat

Failure to launder properly could adversely affect the flame resistance of the fabric.

Ironcat®

FR Treated 100% Cotton Sleeve with Blue/Gold Elastic Ends

- 9 oz. FR treated 100% cotton twill fabric provides durable, breathable comfort for all-day wear
- Blousy fit to protect from an open flame or high heat applications
- Elastic ends provides a snug fit and helps eliminate debris from entering the sleeve
- Offers protection in low heat and light spark applications
- Flame-resistant and washable to maintain performance through repeated laundering
- Certified to ISO 11611, ISO 11612, and ASTM D6413

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-16

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
7042/14	Green	14"	616314906480	10616314906487	20616314906484
7042/18	Green	18"	662909004727		10662909004724