



Siemens Low Voltage's Multi-Family Metering Line of PAK Metering:
Standard 125A as part of the PAK Metering: Standard 125A Group. Type:
UNI-PAK Features: HORN BYPASS Appn: GARDEN - STYLE Std: UL-
50,67,414 V. Rating: 120/240V A. Rating: 600A phase: 1PH size:
9.000x45.07 x 39.690 No. Of Cutouts: 17 Cutout Size: 1 x (1/2,3/4,1,1-
1/4"), 12 x (2-1/2,2,1-1/2,1-1/4,1"), 2 x (4,3-1/2,3,2-1/2,2"), 2X4" Cable
Entry: TOP OR BOTTOM FEED Terminal: 3X2 STUDS. Insulated.Appn.:
Wall Mounted. Enclosure: RINGLESS

cable entry type	TOP OR BOTTOM FEED
fastening method	WALL MOUNTED
suitability for operation	GARDEN-STYLE
ampacity	600 A
product brand name	Siemens
product type designation	UNI-PAK
special product feature	HORN BYPASS
design of the terminal strip	3X2 STUDS
certificate of suitability	UL-50;67;414

last modified:

3/23/2020 