

Project Name

Location

Prepared By



## NUVO 62-1875

LED GLAMOUR BN 10" FLUSH

### Notes

[www] 06-11-2023 09:31:01

### General

Status	Active
Collection	Glamour
Finish	Brushed Nickel
Wattage	18W
Style	Transitional
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm White to Natural Light
Width (in.)	9.84
Height (in.)	2.13
Indoor or Outdoor Fixture	Indoor

### Smart Product Info

IOT Enabled	No
Integrated Camera	No

### Specifications

Technology	LED
CRI	90+
Lumen Output	968L/991L/1050L/1091L/1104L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Weight (lb.)	1.25
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Flush Mount
Operating Temperature	-20C (-4F) to +40C (+104F)

### Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

### Additional Information

Warranty	5-Years
----------	---------