



MCR
SAFETY

BearKat (BK1)

Safety Glasses

Value Series

Specification Sheet

PRODUCT DESCRIPTION:

The BearKat® BK1's super well thought-out construction combines the best in safety, comfort, and affordability! Your vision is unobstructed by the one-piece wraparound lens, which by its tight fit allows you maximum safety. Comfort is enhanced by the flexible temples and the non-slip temple sleeves are notched for a clip-on breakaway cord. Choose the best safety glasses, choose MCR Safety!



FEATURES:

- Strong yet lightweight design
- Single lens design with integral side shields for unobstructed view
- Non-Slip soft temple material
- Exclusive Duramass® scratch resistant coating
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays
- ANSI Z87+ and CSA Z94

TECHNICAL DATA FOR: BK112

| | | | |
|--------------------------|--------------------------|----------------------|------------|
| Series | BearKat (BK1) | ANSI Z87+ | Yes |
| Category | Safety Glasses | CAN/CSA Z94.3 | Yes |
| Scratch Resistant | Yes | AS/NZS 1337.1 | Yes |
| Packaging | White Inner Box | CE EN166 | Yes |
| Case Pack | 144 | Case Weight | 13.698 lb. |
| Case Dimensions | 22.835 x 14.567 x 12.992 | Made In | Taiwan |

| Item No: | Lens Options: | Lens Coating: | Scratch Resistant: | VLT%: | Frame Color: | Temple Color: | Temple Sleeve: |
|----------|---------------|--------------------|--------------------|-------|--------------|---------------|----------------|
| BK010 | Clear | Uncoated | No | 90 | N/A | Clear | Black |
| BK012 | Gray | Uncoated | No | 13 | N/A | Gray | Black |
| BK110 | Clear | Duramass Hard Coat | Yes | 90 | N/A | Clear | Black |
| BK110AF | Clear | UV-AF Anti-Fog | Yes | 90 | N/A | Clear | Black |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved



MCR
SAFETY

BearKat (BK1)

Safety Glasses

Value Series

Specification Sheet

| Item No: | Lens Options: | Lens Coating: | Scratch Resistant: | VLT%: | Frame Color: | Temple Color: | Temple Sleeve: |
|----------|------------------|--------------------|--------------------|-------|--------------|---------------|----------------|
| BK112 | Gray | Duramass Hard Coat | Yes | 13 | N/A | Gray | Black |
| BK112AF | Gray | Duramass Anti-Fog | Yes | 13 | N/A | Gray | Black |
| BK113 | Light Blue | Duramass Hard Coat | Yes | 68 | N/A | Light Blue | Black |
| BK114 | Amber | Duramass Hard Coat | Yes | 80 | N/A | Amber | Black |
| BK116 | Orange | Duramass Hard Coat | Yes | 57 | N/A | Orange | Black |
| BK117 | Silver Mirror | Duramass Hard Coat | Yes | 13 | N/A | Smoke | Black |
| BK118 | Blue Mirror | Duramass Hard Coat | Yes | 13 | N/A | Smoke | Black |
| BK119 | I/O Clear Mirror | Duramass Hard Coat | Yes | 36 | N/A | Clear | Black |
| BKH10 | Clear | Duramass Hard Coat | Yes | 90 | N/A | Clear | Black |
| BKH10G | Gray | Duramass Hard Coat | Yes | 13 | N/A | Gray | Black |
| BKH15 | Clear | Duramass Hard Coat | Yes | 90 | N/A | Clear | Black |
| BKH15G | Gray | Duramass Hard Coat | Yes | 13 | N/A | Gray | Black |
| BKH20 | Clear | Duramass Hard Coat | Yes | 90 | N/A | Clear | Black |
| BKH20G | Gray | Duramass Hard Coat | Yes | 13 | N/A | Gray | Black |
| BKH25 | Clear | Duramass Hard Coat | Yes | 90 | N/A | Clear | Black |
| BKH25G | Gray | Duramass Hard Coat | Yes | 13 | N/A | Gray | Black |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved