

STONEY

PFL2560-PBR

The architectural design language of the Stoney family is softened by its unique material qualities. Large conical white linen shades are edged with contrasting whip-stitching, echoing the natural jute wrap details along the Patina Brass frames. Available as a 1-light sconce, 1-light pendant, 5-light chandelier, and 1-light floor lamp, Stoney is an ode to craftsmanship.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 59.75"

Width/Diameter: 22"

Length: 18"

Canopy/Backplate: 11.75"

Product Weight: 26lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Textile

Shade 1 Finish: White Linen

Shade 1 Top Width: 2.75"

Shade 1 Bottom L/W: 18" / 0"

Shade 1 Height: 10.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 96"

Cord Type: SPT-2 BLACK FABRIC

Switch Type: ON/OFF STOMP SWITCH

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 40" x 20" x 24"

Carton 1 Weight: 40lb

Shipping Method: Ground

Country of Origin: VN

